

Ordering Data SIMATIC TOP connect. The flexible connection for SIMATIC S7.



Front connector with single cores for SIMATIC S7

Description Length¹⁾

SIMATIC S7-300 (16 I/O)

Core type H05V-K

20 x 0.5 mm ² with screw connection	2.5 m
20 x 0.5 mm ² with screw connection	3.2 m
20 x 0.5 mm ² with screw connection	5 m
20 x 0.5 mm ² with crimp connection	2.5 m
20 x 0.5 mm ² with crimp connection	3.2 m
20 x 0.5 mm ² with crimp connection	5 m

Core type UL/CSA-certified

20 x 0.5 mm ² with screw connection	3.2 m
20 x 0.5 mm ² with screw connection	5 m

SIMATIC S7-300 (32 I/O)

Core type H05V-K

40 x 0.5 mm ² with screw connection	2.5 m
40 x 0.5 mm ² with screw connection	3.2 m
40 x 0.5 mm ² with screw connection	5 m

40 x 0.5 mm ² with crimp connection	2.5 m
40 x 0.5 mm ² with crimp connection	3.2 m
40 x 0.5 mm ² with crimp connection	5 m

Core type UL/CSA-certified

40 x 0.5 mm ² with screw connection	3.2 m
40 x 0.5 mm ² with screw connection	5 m

SIMATIC S7-400 (32 I/O)

Core type H05V-K

46 x 0.5 mm ² with screw connection	2.5 m
46 x 0.5 mm ² with screw connection	3.2 m
46 x 0.5 mm ² with screw connection	5 m

46 x 0.5 mm ² with crimp connection	2.5 m
46 x 0.5 mm ² with crimp connection	3.2 m
46 x 0.5 mm ² with crimp connection	5 m

Core type UL/CSA-certified

40 x 0.5 mm ² with screw connection	3.2 m
40 x 0.5 mm ² with screw connection	5 m

1 pc.

Order No.

6ES7922-3BC50-0AB0
6ES7922-3BD20-0AB0
6ES7922-3BF00-0AB0
6ES7922-3BC50-0AF0
6ES7922-3BD20-0AF0
6ES7922-3BF00-0AF0

6ES7922-3BD20-0UB0
6ES7922-3BF00-0UB0

6ES7922-3BC50-0AC0
6ES7922-3BD20-0AC0
6ES7922-3BF00-0AC0

6ES7922-3BC50-0AG0
6ES7922-3BD20-0AG0
6ES7922-3BF00-0AG0

6ES7922-3BD20-0UC0
6ES7922-3BF00-0UC0

6ES7922-4BC50-0AD0
6ES7922-4BD20-0AD0
6ES7922-4BF00-0AD0
6ES7922-4BC50-0AE0
6ES7922-4BD20-0AE0
6ES7922-4BF00-0AE0

6ES7922-4BD20-0UD0
6ES7922-4BF00-0UD0

Set of 5

Order No.

6ES7922-3BC50-5AB0
6ES7922-3BD20-5AB0
6ES7922-3BF00-5AB0

6ES7922-3BC50-5AC0
6ES7922-3BD20-5AC0
6ES7922-3BF00-5AC0

6ES7922-4BC50-5AD0
6ES7922-4BD20-5AD0
6ES7922-4BF00-5AD0
6ES7922-4BC50-5AE0
6ES7922-4BD20-5AE0
6ES7922-4BF00-5AE0

¹⁾ Special lengths on request