

Questionnaire SIWAREX

Customer information

Contact: _____

E-mail: _____

Company: _____

Prepared by: _____

Address: _____

Date: _____

City: _____ Country: _____

Notes on application: _____

Zip/Postal Code: _____ Phone: (_____) _____

Fax: (_____) _____

Electronics

Application type

Non Automatic Weighing Instrument

Truck/Wagon scale static

Checkweigher

Platform Scale

Automatic filling/Big Bag scale

Solid flow meter

Vessel/Silo/level measurement

Dosing scale

Weighfeeder

Truck scale

Belt scale

Loss in weight dosing scale

Force measurement

Type of material: _____

Requested features

Basic weighing functions

Error control and logging

Fast weight value processing

Recording of weighing sequence

Preventive diagnostics

Legal-for-trade

With Ex approval

Zone type/number: _____

CPU integration

SIMATIC S7-200 directly SIMATIC S7-1200 SIMATIC PCS7 Version: _____ Other

SIMATIC S7-300 directly SIMATIC S7-1500 WINCC flex Version: _____ Name: _____

SIMATIC S7-300/400 with bus Type: _____

SIWAREX Mechanic

Load cells

Total maximum weight: _____

Dead load : _____

Required precision: _____

Load cells quantity: _____

Number of support points: _____

Vibration (Motor, Mixer, etc.)

Guide elements required?

Lift up protection

Diagnostics

High overload protection

High measuring rate

Ex Protection

Stainless steel required?

Special application requirements

Pictures available

Drawing available

Retrofit of an old installation