

NPI solutions for electronics

Automated programming and document generation for PCB assembly

SIMATIC IT Unicam

Answers for industry.

SIEMENS

Simatic IT for the electronics industry

Electronics manufacturers must bring cost-effective products to market faster than ever while meeting a variety of challenges including the introduction of a large number of new products in record time; manufacturing a growing mix of complex products; meeting customer and regulatory demands like traceability and lead free manufacturing; and introducing new technologies, being components, software, equipment or processes.

Beyond these day-to-day manufacturing challenges, global electronics manufacturers face the challenge of acquiring new facilities; selecting the right equipment; balancing the workload between factories; managing inventory and quality on a global scale; and managing the outsourcing business process.

Simatic IT for Electronics manufacturing addresses these critical issues, by providing the most commonly used manufacturing process management solution for designing, managing and integrating the NPI process, seamlessly combining and integrating it with the production execution on the shop floor and the outsourcing business process at the single plant, corporation or extended enterprise levels.


Use this complete, end-to-end manufacturing solution to design, optimize and execute board and boxlevel production processes. Simatic IT helps you introduce new products faster by more easily programming and optimizing the widest variety of assembly machines and test equipment in low and high mix scenarios, logging defects in the repair process and managing all aspects of manufacturing execution, from material management, to machine monitoring to quality management to full product and process traceability.

Siemens solutions for electronics manufacturing

Simatic IT helps manufacturers implement effective electronics manufacturing strategies – from sharing product and process designs, to joint process planning and engineering by teams in distributed locations – helping planners to make decisions such as where, how and with what resources to manufacture products.

Simatic IT is an end-to-end collaborative solution that enables the planning, design, analysis, optimization and operation of manufacturing processes – letting users create and share manufacturing information across the enterprise and throughout the supply chain.

Leading manufacturers around the world which are adopting Siemens solutions to expand revenue potential by accelerating product introductions, reducing costs, shortening time to volume and optimizing production execution.





NPI solutions for electronics - Simatic IT Unicam Automated programming and document generation for PCB assembly

Simatic IT UniCam software from Siemens is the electronic industry's leading solution for PCB assembly. Users will enjoy the same benefits of the original UniCam in an updated working environment enabling greater ease of use with additional functionality. For new users, Simatic IT UniCam provides a solid entry solution for standardizing PCB Assembly process planning, machine programming and generating process documentation and hand insert instructions.

Whether you are a veteran user, or are seeking a solid PCB assembly solution for machine programming and document generation, Simatic IT Unicam is an ideal solution that addresses fundamental new product introduction (NPI) requirements.

Longtime UniCam users will enjoy a significant upgrade. Simatic IT Unicam offers flexibility in file management including support of long file names and can be installed on Windows 2000, 2003 and XP.

Additional features include enhanced user friendliness with better navigation via a configurable quick user menu, standardized library editing for faster job processing and additional interfaces for both CAD import and machine output.

New users will enjoy the benefits of the most commonly used NPI tool for PCB Assembly in an updated interface.

With a ten year track record and more than 1,000 global users, UniCam FX is a proven solution for your PCB Assembly programming and documentation needs.

Simatic IT Unicam now supports long file names and may be installed on Windows 2000 and XP. As a 32-bit solution, processing speed is considerably faster allowing users to better cope with demanding environments.

Quick menu

A quick menu has been integrated into the Simatic IT Unicam user environment to allow faster navigation and better solution interfacing. The quick menu is not configurable.

CAD import

Siemens software provides the most complete and current CAD readers available for electronics manufacturers. Users can capture full CAD including nets and traces from over 65 different platforms. Regular updates insure that users can import CAD files from the most current versions in the marketplace.

Library editor

A standard library editor is available for editing parts, shapes and machine libraries. Being standard, users can speed up their overall processing with a common editing interface.

Factory definition

With more than one hundred SMT, THT, screen print and glue machines supported PCB assembly process models may be built and retained as resource libraries. Furthermore, hand insert stations can be defined including specific station configurations.

With the factory defined, Simatic IT Unicam is able to assign process components across the selected production line.

Documentation and work instructions

Simatic IT Unicam automatically generates full sets of documents including setup lists, assignment sheets and hand insert instructions. Documents are generated in user configurable templates.


Drawing files may be imported into the instructions. Any engineering changes will update the entire set of documents.

Viewing and query

Viewing capabilities are available with deployable standalone view stations that may be installed on a network or at distributed locations.

Board layout and circuits may be viewed and queried speeding up collaboration between different process engineering teams within a single site or across an enterprise.

View stations may also be used for electronic publication of documents and work instructions enabling faster delivery to operators and creating a paper-free environment.



Features:

- Import native CAD from 65 different platforms including nets and traces
- Automates assignment between different processes across the PCB assembly line
- Machine program generation for 100 different platforms including the most commonly used SMT, THT and dispenser equipment
- Automated generation of manufacturing documents and hand insert instructions within user configurable templates
- 2D viewing capabilities, query including first article inspection and electronic publishing of documents and work instructions

Benefits:

- Fast and accurate CAD/BOM recovery including part shapes and net traces
- Process assignment across the PCB assembly line in minutes rather than hours
- Machine programs generated in minutes including support of mixed lines
- Full sets of documentation including hand insert instructions are automatically generated within user defined templates

Get more information

www.siemens.com/mes-simaticit
marketing.simatic-it@siemens.com

Siemens AG
Industry Sector
Industry Automation

www.siemens.com/mes-simaticit

Subject to change without prior notice
© Siemens AG 2008

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.